

# Turning your ideas into reality. Since 1986





Individuals created the world around us by giving form to their dreams and ideas. We believe imagination and ideas are our most powerful force, opening up limitless possibilities. Our goal is to provide everyone the ability to turn their creativity into the satisfaction of monozukuri -the enjoyment of making things. monoFab desktop tools are based on the 3D modeling technology that Roland DG pioneered and has continually enhanced since 1986. Incorporating both additive and subtractive 3D monoFab technologies, you can now realize your creativity like never before. The fabrication facility of the future is here -- right on your own desk.



### Roland OnSupport ensures convenience and peace of mind



Roland OnSupport software connects lifestyles with resources and increases the efficiency of our products. Software updates are available through OnSupport. In addition, notifications of completed production and job reports are sent directly to your cell phone or computer so you can be confident in knowing the progress of your models, even when you are away from your desk. \*Use of Roland OnSupport requires an Internet connection.


Download software updates and drivers.
Now you can concentrate on other tasks and an email will keep you informed of the job status.
Support information for your model is accessible with just one mouse click. No more frustration and wasted time trying to find what you need.
Improve your skills with useful information available exclusively

# Unmatched service and support

through OnSupport.



Roland DG Academy: To get the most from your product, take advantage of our extensive training resources worldwide. Roland Academy teaches everything from product basics to







customer services is offered.

Roland DG products that feature this environmental label meet the company's criteria for environmental consciousness, a set of standards based on ISO 14021 self-declaration type II. For more information, please visit www.rolanddg.com.

### monoFab ARM-10



Specificati	ons (ARM-10)		
Bui <b>l</b> d techno	logy	Layer projection system	
Build size		130 (W) $\times$ 70 (D) $\times$ 70 (H) mm (5.1 (W) $\times$ 2.7 (D) $\times$ 2.7 (H) inches) (Job volume of resin is up to 300 g (0.7 lbs))	
Build speed		10 mm/h (Layer pitch = 0.15 mm)	
Light source		UV-LED (ultraviolet light emitting diode)	
XY resolution	١	0.2 mm	
Z axis reso <b>l</b> u	tion	0.01mm	
Power requir	ements	Machine: DC 24 V, 0.6 A, Dedicated AC adapter: AC 100 V to 240 V±10%, 50/60 Hz	
Power consu	mption	15 W	
Acoustic noi	se level	During operation: 55 dB (A) or less, During standby: 49 dB (A) or less	
Dimensions,	/ Weight	430 (W) $\times$ 365 (D) $\times$ 450 (H) mm (17.0 (W) $\times$ 14.4 (D) $\times$ 17.8 (H) inches) / 17 kg (37.5 lbs)	
Interface		USB	
Environment	During operation	Temperature of 20 to 30°C, 68 to 86°F, 35 to 80% relative humidity (non-condensing)	
Livironmeni	Not operating	Temperature of 5 to 40°C, 41 to 95°F, 20 to 80% relative humidity (non-condensing)	
Included iten	ns	AC adapter, Power code, USB cable, Liquid material vat, Printing and washing tools (Metallic spatula, Plastic spatula, Tweezers, Washing container x 2, Hexagonal wrench, Spanner, Rubber gloves, Work tray, etc.), Start-up page information card, Read this first.	

### monoFab SRM-20

ications (SRM-20)			20.2
e material	Resins such as chemical wood and modeling wax (metal not supported), substrates for machining	Collets (for end-mills)	ZC-2
nd Z operation strokes	203.2 (X) x 152.4 (Y) x 60.5 (Z) mm (8 (X) x 6 (Y) x 2.38 (Z) inches)		ZC-2
from collet tip to table	Maximum 130.75mm (5.15 inches)	Other	
ize	232.2 (X) x 156.6 (Y) mm (9.14 (X) x 6.17 (Y) inches)	Spindle motor	SM-2
le workpiece weight	2 kg (4.4 lbs)	Spindle unit	SS-20
nd Z-axis drive system	Stepping motor	Unit: mm, dia. = flute diameter, F	R = flute rad
ing speed	6 ~ 1800mm/min (0.24 ~ 70.87inches/min)	L = overall length, NT = number of flutes	
e resolution	0.01 mm/step (RML-1), 0.001 mm/step (NC code) (0.00039 inches/step (RML-1), 0.000039 inches/step (NC code))	System Requirements (A	NDA4 10
nical resolution	0.000998594 mm/step (0.00000393 inches/step)		
motor	DC motor Type 380	Operating system	Wind
um spindle rotation	7,000 rpm	CPU	Intel®
tool chuck	Collet method	RAM	1GB
е	USB	Video card and monitor	A res
command sets	RML-1, NC code	Free hard-disk space	100
requirements	Machine: DC24V, 2.5A, Dedicated AC adapter: AC 100V±10%, 50/60Hz		Interr
consumption	Approx. 55W	Other requirements	Interr
c noise level	During operation: 65 dB (A) or less (when not cutting), during standby: 45 dB (A) or less	*Roland OnSupport and included	
ions / Weight	451.0 (W) x 426.6 (D) x 426.2 (H) mm (17.76 (W) x 16.80 (D) x 16.78 (H) inches) / 19.6 kg (43.2 lbs)	WoW64 (Windows 32-bit on Wi	
ment	Temperature of 5 to 40°C (41 to 104 °F), 35 to 80% relative humidity (non-condensing)		
d items	AC adapter, Power cord, USB cable, Cutting tool, Collet, Set screw, Spanners (7,10mm / 0.28, 0.39 inches), Hexagonal wrench (size 2,3 mm / 0.08, 0.12 inches), Positioning pins, Double-sided tape, Start-up page information card, Read first(Booklet)		

## Item Model tesin PRH35-ST 350 g bottle iquid material vat LMV-10 For replacement

ltem .	Model	Description
End-mi <b>ll</b> s		
	ZHS-100	High speed steel dia. 1 3(ℓ)×6(d)×50(L)×2NT
	ZHS-200	High speed steel dia. 2 6(ℓ)×6(d)×50(L)×2NT
Square end-mi <b>ll</b> s	ZHS-300	High speed steel dia. 3 10(ℓ)×6(d)×50(L)×2NT
	ZHS-400	High speed steel dia. 4 12(ℓ)×6(d)×50(L)×2NT
	ZHS-500	High speed steel dia. 5 15(1)×6(d)×55(L)×2NT
	ZHS-600	High speed steel dia. 6 15(ℓ)×6(d)×55(L)×2NT
	ZHS-3015	High speed steel dia. 3 15(ℓ)x6(d)x50(L)x2NT; 2piece
	ZCB-150	Cemented Carbide R1.5 25( ll)×2.4(Lc)×65(L)×6(d)×2NT
Ball end-mills	ZCB-200	Cemented Carbide R2 25( \ell )×3.2(Lc)×70(L)×6(d)×2NT
	ZCB-300	Cemented Carbide R3 30( & )×4.8(Lc)×80(L)×6(d)×2NT
Engraving cutters		

cutters (tor plastic)	ZEC-100	Cemented Carbide dia. 6x50 (L)x0.225 (W)
	ZC-20-30	dia. 3 mm
end-mi <b>ll</b> s)	ZC-20-32	dia. 3.175 mm
ena-mins)	ZC-20-40	dia. 4 mm
	ZC-20-60	dia. 6 mm

motor	SM-20	For replacement	
unit	SS-20	For replacement	
dia. = flute diameter. R =	flute radius. La	= cutting lergth, I = flute length, d = shank diameter.	

uirements (ARM-10/SRM-20)			
stem	m Windows® 7/8/8.1 (32-bit/64-bit edition)*		
	Intel® Core™ 2 Duo or more (Core™ i5 or more recommended)		
	1GB (2GB or more recommended)		
nd monitor	A resolution of 1,280x1,024 or more recommended		
space	100 MB or more recommended		
ments	Internet connection and web browser, Internet Explorer® version 10 or more recommended		

\*Roland OnSupport and included software for SRM-20 are 32-bit application, which run on 64-bit Windows® with

Roland reserves the right to make changes in specifications, materials or accessories without notice. Your actual output may vary. For optimum output quality, periodic maintenance to critical components may be required. Please contact your Roland dealer for details. No guarantee or warranty is implied other than expressly stated. Roland shall not be liable for any incidental or consequential damages, whether foreseeable or not, caused by defects in such products. All trademarks are the property of their respective owners. Three-dimensional shapes may be protected under copyright. Reproduction or use of copyrighted material is governed by local, national, and international laws. Customers are responsible for observing all applicable laws and are liable for any infringement. Roland DG Corporation has licensed the MMP technology from the TPL Group.





Printed in Japan. RDG-416100999 AUG 14 D-3 D-S

www.rolanddg.com















3D Modeling

3D CAD/CG data is opened in the

included Roland software where it is

optimized for either 3D printing or milling.




3D Printing

### ARM-10

By using the ARM-10 3D printer, designs which would challenge standard milling, such as undercuts and complex shapes, can be produced with just a few software steps. Your ideas are transformed into tangible 3D objects







3D Milling

# A CREATOR'S VIEW



The next evolution in compact milling machines

"Allowing the user to personally experience aspects of both design and engineering"

### — The actual 3D sample production process

I produced an active speaker prototype using monoFab. I used the ARM-10 3D printer to produce the external parts since these shapes are complex, and used the SRM-20 milling machine to model the cabinet where milling precision as well as selecting the suitable material was required. In this way, I made the most of the respective strengths of the 3D printer and the milling machine, using them each as appropriate for the purpose and form. By using 3D printers and milling machines together, work can quickly progress to significantly reduce workflow. Actually, I think this probably made it possible to produce a sample in a much shorter time than usual. It also frees up time to try out additional ideas, and if mistakes are made early on in the prototype stage, these can be used to generate feedback that will result in production of a final version with greater precision.

— How can monoFab be leveraged in the design process?


What is really important in product design is to create beautifully comfortable designs. Furthermore, it is required to consider what type of personal experience is ultimately delivered and which enjoyable things can be proposed to the user. it's not really possible, however, to share personal experience through sketches or words alone. At times like that, the use of 3D printers or milling machines to give form to objects delivers something that can be touched by hand and truly experienced, which can then be used to check user-friendliness. It's even possible to grasp structural inconsistencies at early stages that could not be seen in sketches. With monoFab and its two means of expression – printing and milling – I thought this would provide a powerful tool for creating personal experiences through prototyping, not only in design but also in > www.rolanddg.com/monofab/interview/01.html

### Projector-type 3D printer fits on your desk

The newly developed desktop ARM-10 3D printer brings together Roland DG's 3D modeling technologies. It features a proprietary

projector lens and Roland's imageCure resin, creating 3D models using UV light. The acrylic resin becomes semi-transparent when cured. Post-processing, such as support removal, polishing, and adding color are simple to do.






The UV lamp instantly cures and laminates acrylic resin to build 3D shapes. The projection system allows simultaneous production of multiple objects within the same work area, enabling efficient 3D printing.

### Roland software supports 3D printing operation even for novice users

monoFab Player AM enables data correction, with a healing function to fill in any gaps in 3D data and simplification of meshes, layout editing and automatic support generation. The user-friendly interface is easy to use, making it ideal even for beginners.



### Create complex shapes with minimum resin consumption

With 3D printing, parts which previously required multi-axis milling, such as complex objects with undercuts, can be built quickly and easily. By using a suspended build system, resin consumption is kept to a minimum, making model production efficient and affordable.

Includes support tray and containers to remove excess uncured resin. Also spatula and tweezers for support removal.



# MILLING MACHINE

A real prototype can be manufactured at an early

inspection of aesthetics, structure, movement, fit, etc.

Modifications to the design can then be made at the

stage of the design process, enabling detailed

most effective time, without additional costs.

monoFab

**SRM-20** 

Check

# Desktop milling machine for precision 3D modeling



## Designed for clean and secure use in your office or classroom

The SRM-20 includes an interlocked full cover and a dust-collection tray to keep your environment clean and clear of waste material. For increased safety, opening the cover automatically stops the machine



### Simple operation for optimum results

The SRM-20 is Roland's latest generation desktop milling machine for the Designed for ease of use, the SRM-20 supports Roland's unique "VPanel," office, studio and educational environment. Since pioneering desktop milling an on-screen operation panel for the computer. By using the speed-controlled in 1986, Roland has continued to perfect our expertise in delivering accuracy 4-way cursor movement, the origin point can be set and efficiency in a compact format. The SRM-20 incorporates innovative quickly and accurately. Spindle RPM and milling features, including a new spindle, collet, circuit boards and control software. speed can be altered during milling, allowing full control over the results and milling time.

## 3 types of software included for ease of use, even for beginners

MODELA Player 4 is a CAM software that automatically calculates and displays the cutting tool path from 3D data created in commercial 3D CAD software or downloaded from the Internet. iModela Creator is a 2D milling software for processing 2D data such as text and graphics. ClickMILL provides the user with direct control of the machine without the need to access CAD or CAM software when drilling holes or cutting pockets and other finishing processes. All software can be used individually as needed.





> www.rolanddg.com/monofab/

Roland®